

Grab Rail Clean Seal with Easy Slider Model No. GCSS1040E



SPECIFICATION

Clean seal fully welded construction is finished in satin stainless steel tubing with double chrome plated innovative flange and cover system. Simple fixing method with a hygienically sealed installation with silicone 'o' ring seals. Designed for the safety, security and convenience of the physically disabled. Easy to install on most building surfaces. Tubing diameter is 32mm.

Includes premium designed durable cast alloy cradle with fully adjustable sliding tension for rail and the handset pivot incorporating a self-cleaning slide with anti-rotate feature. GCSS1040E includes chrome shower kit Model No. SK-HSKF

RECOMMENDED INSTALLATION HEIGHT

To comply with Australian Standards AS 1428.1, grab rails must be fastened a minimum distance of 800mm from the floor, with 600mm of clear space above the rail and to withstand a force of 1100N at any point from any direction.

WARRANTY

One year.

 $\mbox{Grab}\ \mbox{Rail}\ \mbox{GCSS1040E}$ shall be Model No. GCSS1040E as supplied by ASI JD MacDonald.

All ASI JD MacDonald accessible compliant products when installed must be in accordance with AS1428 to ensure the specified product is complying with all washroom specification requirements.



